

SAISM-4/8S-M12-4P D-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



M12 plug-in connector in IP 67 available with crew or tension clamp connection

General ordering data

Type	SAISM-4/8S-M12-4P D-COD
Order No.	1892120000
Version	Plugs prefabricated to customer spec., M12, pin, straight
GTIN (EAN)	4032248569380
Qty.	1 pc(s).

SAISM-4/8S-M12-4P D-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	44.68 g
------------	---------

Temperatures

Operating temperature range, max.	85 °C	Operating temperature range, min.	-25 °C
Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data customisable plug-in connectors

Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Cable gland	PG 9	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Coding	D	Connection cross-section, max.	0.75 mm ²
Connection cross-section, min.	0.14 mm ²	Contact surface	Gold-plated
Housing main material	CuZn	Insulation resistance	10 ⁸ Ω
No. of poles	4	Plugging cycles	≥ 100
Pollution severity	3	Protection degree	IP67
Rated current	4 A	Rated voltage	250 V
Shield connection	Yes	Temperature range of housing	-40 ... +85 °C
Threaded ring material	Diecast zinc	Type of connection	Screw connection

General Info

Housing main material	CuZn	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Connection thread	M12	Contact surface	Gold-plated
Sheath diameter, min.	6 mm	Sheath diameter, max.	8 mm
Protection degree	IP67	Plugging cycles	≥ 100

Electrical properties

Insulation resistance	10 ⁸ Ω	Rated voltage	250 V
-----------------------	-------------------	---------------	-------

Standards

Connector standard	IEC 61076-2-101	Certificate No. (cURus)	E307231
--------------------	-----------------	-------------------------	---------

Classifications

ETIM 3.0	EC002062	ETIM 4.0	EC002635
ETIM 5.0	EC002635	ETIM 6.0	EC002062
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-01
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-02
eClass 9.1	27-44-01-03		

SAISM-4/8S-M12-4P D-COD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue

[CAT 9 IETH 15/16 EN](#)

[CAT 8 SAI 15/16 EN](#)

[FL FIELDWIRING EN](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)