

MINI-SAS CAGES



✓ Active

PRODUCT DRAWING

English

3D PDF

TE CONNECTIVITY (TE)

MINISAS HD 1X4 REC W/ LP LT PIPE AU ONLY

2274681-1

TE Internal Number: 2274681-1

Always EU RoHS/ELV Compliant

Number of Ports **4**

Number of Rows **2**

Included Lightpipe **Yes**

Keyed **No**

Mounting Style **Through Hole - Press-Fit**

Product Drawings

RECEPTACLE ASSEMBLY, MINI-SAS HD, 4X W/ LOW PROFILE LIGHT PIPES

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Included Lightpipe

Yes

Shell

With

PCB Mounting Orientation

Right Angle

Product Grouping

Mini-SAS HD

Product Type

Cage, Connector

Configuration Features

Number of Ports

4

Number of Rows

2

Keyed	No
Number of Positions	144
Stackable	No
<hr/>	
Contact Features	Contact Base Material
Copper Alloy	
<hr/>	
Termination Features	Termination Post Length
1.64 mm [.065 in]	
<hr/>	
Mechanical Attachment	Mounting Style
Through Hole - Press-Fit	
PCB Mount Retention	With
PCB Mount Retention Type	M2 Screws
<hr/>	
Housing Features	Housing Color
Black	
Housing Material	LCP (Liquid Crystal Polymer)
<hr/>	
Dimensions	Height above PC Board
16.44 mm [.647 in]	
PCB Thickness (Recommended)	.97 mm [.038 in]
<hr/>	
Usage Conditions	High Temperature Housing
Yes	
<hr/>	
Industry Standards	UL Flammability Rating
UL 94V-0	
<hr/>	
Packaging Features	Packaging Method
Tray/Box	
<hr/>	
Product Compliance	Statement of Compliance PDF
VIEW ALL PRODUCT COMPLIANCE	