

Han EMC 40 Hood Top Entry PG 21



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 040 0440
Specification	Han EMC 40 Hood Top Entry PG 21
HARTING eCatalogue	https://b2b.harting.com/09620400440

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Hood

Version

Size	16 B
Version	Top entry
Cable entry	1x Pg 21
Locking type	Screw locking
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	285 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140073517
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors