




Views from "X" rotated



Notes:

Tolerances (unless specified): DIN ISO 2768m

Cable Diameter		Solder Contacts	Crimp Contacts
6 Pole		— — —	KRS6P46-400 1202310094
	Crimp range*		0,75-2,5mm ²
7 Pole		KRS7P46-550 1202310096	KRS7P46-400 1202310098
	Crimp range*		0,75-2,5mm ²
9 Pole (8+1)		KRS9P46-550 1202310100	KRS9P46-410 1202310102
	Crimp range*		0,14-1,0mm ² /0,75-2,5mm ²
12 Pole		KRSCP46-550 1202310104	KRSCP46-010 1202310106
	Crimp range*		0,14-1,0mm ²

*Crimp range only applies to "Crimp Contacts" version

FUNCTIONAL SYMBOLS $\nabla_A=0$ $\nabla_F=0$ $\nabla_P=0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#512581.					molex REC M23 XP XC MA STR M25 BM UNSH BRA							
	MM														NTS		
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
			mm	INCH	EC NO: 753973 DRWN: LIKITV 2023/08/22 CHK'D: ANIKES1 2023/08/30 APPR: GGA 2023/08/31 INITIAL REVISION: DRWN: BBRAUCH 2008/11/17 APPR: JKOLB 2009/03/02					DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
	4 PLACES	± ----	± ----														
	3 PLACES	± ----	± ----														
	2 PLACES	± 0.05	± ----														
	1 PLACE	± 0.1	± ----														
		0 PLACES	± ----	± ----						SD-120231-005		PSD	001	A			
ANGULAR TOL ± ---- °			THIRD ANGLE PROJECTION 					DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								A3-SIZE		120231		SEE TABLE		GENERAL MARKET		1 OF 1	