

## Han B Side Entry LC M20 Exi\_for SL



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® Ex
Type of hood/housing	Hood

### Version

Size	10 B
Version	Side entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Connectors for explosion hazardous environments
Details	ATTENTION! Only to be used with Han® Ex inserts!

### Technical characteristics

Limiting temperature	-20 ... +40 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 With cable gland

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
RoHS	compliant
ELV status	compliant



## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Commercial data

Packaging size	1
Net weight	378 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140181656
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors