



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/30/16	
A		UPDATED PIN ASSIGNMENT	6/22/17	HR/CK
B		UPDATED DRAWING	3/8/19	AY/CK
C		UPDATED DRAWING	5/7/19	AY/AC
D		UPDATE SPEC.	7/5/19	LH/RC



SD-PMAXXX-FFTBR-CXX-XFT
7=IP67 A=UL2464

PART NO.	L
SD-PMAXXX-FFTBR-CXX-3FT	36"±1.80" [914.4±45.72mm]
SD-PMAXXX-FFTBR-CXX-6FT	72"±3.60" [1828.8±91.44mm]
SD-PMAXXX-FFTBR-CXX-10FT	120"±6.000" [3048±152.4mm]



CONTACT : BRASS ; GOLD PLATED.
NUT : BRASS ; NICKEL PLATED.
UL2464 CABLE 2PIN~5PIN 24AWG ; 6PIN~8PIN 26AWG(2A 300V)
OVERMOLD : PVC ; COLOR : BLACK
M12 CONN
DESCRIPTION

SPECIFICATIONS:
Electrical:
Current rating: XXA=1.5A, XXB=2A, XXC=5A
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			TITLE	
DATE			WATERPROOF CONNECTOR, FEMALE, M12 ASSEMBLY CABLE, RIGHT ANGLE	
DRAWN	HR	8/30/16	SIZE	REV.
CHECKED	TW	8/30/16	X	D
APPROVED			SD-PMAXXX-FFTBR-CXX-XFT	
			REF: S00298T	SHEET 1 OF 1
			SCALE: NTS	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SD-PME06A-FFTBL-C7A-6FT](#) [SD-PNL04-FFTAL-SX0-000](#) [SD-PMA04C-FFTBL-C7A-6FT](#) [SD-PME05A-FFTBL-C7A-6FT](#) [SD-PMA05-FFTS5](#) [SD-PME02B-FFTBL-C7A-6FT](#) [SD-PME04B-FFTBL-C7A-6FT](#) [SD-PME03B-FFTBL-C7A-6FT](#)