

Product data sheet

Characteristics

XACA9412

Harmony, round head for push button, spring return, black, booted



Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACA

Complementary

Marking	Unmarked
Operator additional information	Booted
Cap/operator or lens colour	Black
Product compatibility	XACA..
Mounting location	Front of enclosure
Sale per indivisible quantity	10
Standards	CSA C22.2 No 14 UL 508 EN/IEC 60204-32 EN/IEC 60947-5-1
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Oversupply category	Class II IEC 61140
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK08 conforming to EN 50102
Net Weight	0.02 lb(US) (0.01 kg)

Ordering and shipping details

Category	22473 - PUSHBUTTON, PENDANTS
Discount Schedule	CS2
GTIN	00785901645146
Nbr. of units in pkg.	10
Package weight(Lbs)	0.02 lb(US) (0.01 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	4.72 in (12 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	10

Package 2 Weight	3.39 oz (96 g)
Package 2 Height	1.57 in (4 cm)
Package 2 width	3.15 in (8 cm)
Package 2 Length	4.72 in (12 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	700
Package 3 Weight	15.89 lb(US) (7.207 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------