

Han A Hood Coupler Thermoplastic 1 Lever



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 20 003 0727 |
| Specification | Han A Hood Coupler Thermoplastic 1 Lever |
| HARTING eCatalogue | https://b2b.harting.com/19200030727 |

Identification

| | |
|--------------------------|------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han A® |
| Type of hood/housing | Cable to cable housing |

Version

| | |
|----------------------|---|
| Size | 3 A |
| Version | Top entry |
| Cable entry | 1x M20 |
| Locking type | Single locking lever |
| Field of application | Standard Hoods/housings for industrial applications |
| Pack contents | Please order seal screw separately. |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP44 IP65 With seal screw IP67 With seal screw |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|--------------------|
| Material (hood/housing) | Polycarbonate (PC) |
|-------------------------|--------------------|

Material properties

| | |
|---|------------------------------|
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) R23 (HL 1-3) |

Specifications and approvals

| | |
|-----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 12 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |
| GTIN | 5713140124493 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |