

313/315 Series Lead-Free 3AG, Slo-Blo® Fuse



Agency Approvals

Agency	Agency File Number	Ampere Range
	E10480	0.010A - 10A **
	29862	0.010A - 10A **/15A **
	E10480	10A - 30A
	313 Series (Cartridge): NBK060618-E10480A NBK060618-E10480C	1-5A 6.25- 10A **
	315 Series (Leaded): NBK060618-E10480B NBK060618-E10480D	1-5A 6.25-10A **
	SU05001-6004	2.25-2.5A
	SU05001-5007	2.8A - 3.2A
	SU05001-5008	4A - 6.3A
	SU05001-5009	7A-8A
	N/A	0.010A - 10A **

** See note under Electrical Characteristics by item

Additional Information



**Datasheet
313 Series**



**Resources
313 Series**



**Samples
313 Series**



**Accessories
313 & 315 Series**



**Datasheet
315 Series**



**Resources
315 Series**



**Samples
315 Series**

For recommended fuse accessories for this product series, see '[Recommended Accessories](#)' section.

Description

The 3AG Slo-Blo® fuse solves a broad range of application requirements while offering reliable performance and cost-effective circuit protection.

The fuse catalog number with the suffix "ID" instantly identifies itself upon opening by showing a discoloration of its glass body. Guesswork and time consuming circuit testing are eliminated. This unique design offers the same quality performance characteristics as the standard 3AG Slo-Blo® Fuse design.

Features

- Conforms to UL/CSA/ NMX 248-1 and UL/CSA/ NMX 248-14
- RoHS compliant and Lead-free
- Available in cartridge and axial lead format and with various forming dimensions
- Conforms to DENAN's Appendix 3

Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

Electrical Characteristics by Series

% of Ampere Rating	Ampere Rating	Opening Time
100%	10mA – 30A	4 hours, Minimum
135%	10mA – 30A	1 hour, Maximum
200%	10mA – 15A	5 sec., Min., 30 sec., Max
	20A – 30A	5 sec., Min., 60 sec Max


Electrical Characteristic Specifications by Item

Amp Code	Ampere Rating (A)	Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals					
						UL	SP	CCC	RU	PS E	CE
.010	0.01	250	35A@250Vac 10KA@125Vac	4300.0000	0.000121	x	x	-	-	-	x
.031	0.031	250		430.0000	0.00303	x	x	-	-	-	x
.040	0.04	250		300.0000	0.00630	x	x	-	-	-	x
.062	0.062	250		120.0000	0.0210	x	x	-	-	-	x
.100	0.1	250		43.0000	0.0850	x	x	-	-	-	x
.125	0.125	250		30.0000	0.152	x	x	-	-	-	x
.150	0.15	250		20.0000	0.270	x	x	-	-	-	x
.175	0.175	250		8.6700	0.177	x	x	-	-	-	x
.187	0.187	250		8.0100	0.230	x	x	-	-	-	x
.200	0.2	250		6.5900	0.270	x	x	-	-	-	x
.250	0.25	250		4.2700	0.385	x	x	-	-	-	x
.300	0.3	250		3.1350	0.730	x	x	-	-	-	x
.375	0.375	250		2.0950	1.23	x	x	-	-	-	x
.400	0.4	250		1.8750	1.35	x	x	-	-	-	x
.500*	0.5	250		1.2600	2.55	x	x	-	-	-	x
.600	0.6	250		0.9120	4.00	x	x	-	-	-	x
.700	0.7	250		0.7000	5.90	x	x	-	-	-	x
.750	0.75	250		0.6215	7.16	x	x	-	-	-	x
.800	0.8	250		0.5540	8.00	x	x	-	-	-	x
001.*	1	250		0.3750	14.0	x	x	-	-	x	x
01.2	1.2	250	100A@250Vac 10KA@125Vac	0.2780	21.5	x	x	-	-	x	x
1.25	1.25	250		0.2600	24.0	x	x	-	-	x	x
01.5*	1.5	250		0.1910	38.0	x	x	-	-	x	x
01.6	1.6	250		0.1710	49.6	x	x	-	-	x	x
01.8	1.8	250		0.1410	92.0	x	x	-	-	x	x
002.*	2	250		0.1169	77.0	x	x	-	-	x	x
2.25	2.25	250		0.0968	121	x	x	x	-	x	x
02.5	2.5	250		0.0811	199	x	x	x	-	x	x
02.8	2.8	250		0.0675	269	x	x	x	-	x	x
003.*	3	250		0.0593	200	x	x	x	-	x	x
03.2	3.2	250	200A@250Vac 10KA@125Vac	0.0529	209	x	x	x	-	x	x
004.*	4	250		0.0311	76.1	x	x	x	-	x	x
005.*	5	250		0.0214	276	x	x	x	-	x	x
6.25*	6.25	250		0.0154	388	x	x	x	-	x	x
06.3	6.3	250		0.0154	388	x	x	x	-	x	x
007.*	7	250		0.0128	547	x	x	x	-	x	x
008.*	8	250	300A@32Vac	0.0111	701	x	x	x	-	x	x
010.**	10	250		0.0083	1285	x	x	-	-	x	x
010.*	10	32		0.0083	1285	-	-	-	x	-	-
012.	12	32		0.0065	1200	-	-	-	x	-	-
015.	15	32		0.0050	2650	-	-	-	x	-	-
020.	20	32		0.0022	9560	-	-	-	x	-	-
025.	25	32		0.0017	16500	-	-	-	x	-	-
030.	30	32		0.0012	26900	-	-	-	x	-	-

* For 313series, these ratings available with an indicating option. Add the "ID" designation to the series number. i.e. 313.500ID.

** The 10A is designed for special voltage requirement. Available as 250Vac rated and the part number is 0313010.MX250P


Temperature Re-rating Curve




A - For 313/315 Series, from 10mA to 150mA
B - For all other ampere ratings of 313/315 series

Note:
Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation
Preheat: (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100°C
Temperature Maximum:	150°C
Preheat Time:	60-180 seconds
Solder Pot Temperature:	260°C Maximum
Solder Dwell Time:	2-5 seconds

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C
Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width
313 Series				
Bulk	N/A	1000	MX	N/A
Bulk	N/A	100	HX	N/A
315 Series				
Bulk	N/A	1000	MX	N/A
Bulk	N/A	100	HX	N/A
Bulk	N/A	1000	MXB	N/A


Product Characteristics

Materials	Body: Glass Cap: Nickel-plated brass Leads: Tin-plated Copper
Terminal Strength	MIL-STD-202, Method 211, Test Condition A
Solderability	MIL-STD-202 method 208
Product Marking	Cap1: Brand logo, current and voltage ratings Cap2: Series and agency approval marks

Operating Temperature	-60°C to +125°C*
Thermal Shock	MIL-STD-202, Method 107, Test Condition B: (5 cycles -65°C to +125°C)
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A: High RH (95%) and Elevated temperature (40°C) for 240 hours
Salt Spray	MIL-STD-202, Method 101, Test Condition B


* See Temperature Re-rating Curve

Dimensions



Measurements displayed in millimeters (inches)

Part Numbering System



Recommended Accessories

Accessory Type	Series	Description	Max Application Voltage	Max Application Amperage
Holder	155100	Twist-Lock In-Line Fuseholder	32	20
	342	Traditional Panel Mount Fuseholder	250	20
	346	Panel Mount Flip-Top Shock-Safe Fuseholder	250	15
	345	Shock-Safe Fuseholder with PC Mount, Solder Mount and Panel Mount options	250	16
Block	354	Low Profile OMNI-BLOK® Fuse Block	600	30
	359	High Current Screw Terminal Fuse Block		30
Clip	122	High Current Traditional PC Board Fuse Clip	1000	30
	101	Rivet/Eyelet Type Fuse Clip	1000	15

Notes:

- Do not use in applications above rating.
- Please refer to fuseholder data sheet for specific re-rating information.
- Please contact factory for applications greater than the max voltage and amperage shown.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[313005P](#) [0313001.H](#) [0313015.H](#) [0313.250H](#) [0313015.M](#) [0313.375M](#) [0313.800H](#) [0313005.H](#) [0313001.M](#)
[031302.5H](#) [031306.3M](#) [0313025.M](#) [0313.700H](#) [031301.2M](#) [0313.125M](#) [0313008.HXID](#) [0313.300H](#) [031301.5M](#)
[0313005.HXID](#) [0313.300M](#) [031301.5HXID](#) [0313.375H](#) [0313010.H](#) [0313.600M](#) [03136.25H](#) [0313.100H](#) [0313.187M](#)
[0313.125H](#) [0313.600H](#) [031301.8H](#) [031302.5M](#) [0313.100M](#) [0313002.H](#) [0313002.HXID](#) [0313005.M](#) [0313.800M](#)
[0313007.M](#) [031303.2M](#) [031301.6M](#) [0313.250M](#) [03136.25HXID](#) [0313.700M](#) [031301.8M](#) [313030P](#) [0313.031H](#)
[0313030.H](#) [031302.8H](#) [0313007.H](#) [313.062P](#) [313.100P](#) [313.125P](#) [313.250P](#) [313001P](#) [31301.5P](#) [31302.5P](#)
[31501.5P](#) [313003P](#) [31303.2P](#) [3136.25P](#) [313015P](#) [313010P](#) [313.400P](#) [313.700P](#) [0313008.M](#) [0313.010H](#)
[0313.500HXID](#) [0313004.M](#) [0313012.H](#) [0313025.H](#) [0313008.H](#) [031303.2H](#) [0313.150M](#) [0313030.M](#) [031306.3H](#)
[0313.031M](#) [031301.5H](#) [0313020.M](#) [03131.25M](#) [03132.25M](#) [0313012.M](#) [0313.750M](#) [031301.6H](#) [0313.040H](#)
[031302.8M](#) [0313020.H](#) [0313.062H](#) [0313.062M](#) [0313002.M](#) [0313004.H](#) [0313003.H](#) [0313.175M](#) [0313.010M](#)
[0313.150H](#) [0313.175H](#) [0313.187H](#) [0313007.HXID](#) [0313.040M](#) [0313001.HXID](#) [0313010.HXID](#) [03132.25H](#)