




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	1b/2a
Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Locking Latch Between Cavity Number	1&2
Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Connector Length	10 mm[.39 in]
Connector Height	12.2 mm[.48 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

RAST Version	02-A
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	2500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 928344-3
3P STD TIMER GEH

TE Part # 2-928344-6
STD TIM GEH 6P

TE Part # 928343-2
STD-TIM GEH 2P

TE Part # 8-928344-2
STD-TIMER GEH 2P

TE Part # 928344-7
7P STD-TIMER GEH

TE Part # 928344-4
4P STD TIMER GEH

TE Part # 3-928344-4
4P STD TIMER GEH

TE Part # 5-928344-4
STD TIMER HOUSING 4POS



TE Part # 1-928344-2
STD-TIMER GEH 2P

TE Part # 1241981-3
STD TIMER HOUSING 3P (NATURE)

TE Part # 7-928344-2
STD-TIMER GEH 2P

TE Part # 928344-5
5POS STD TIM HOUSING W.
INTERIOR LOCKING

Also in the Series | RAST 5 IDC Connectors

Automotive Terminals(8)

Connector Contacts(14)

Crimp Terminal Housings(39)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(417)

Rectangular Connector Housings(1)

Standard Edge Connectors(32)

Standard Rectangular Connectors(63)

Wire-to-Board Connector Assemblies
& Housings(202)

Customers Also Bought

TE Part #178307-2
DYNAMIC D3100 HDR ASSY 16P

TE Part #177900-1
POWER DBL LOCK PLUG HSG 4P

TE Part #964204-1
STD-POW-TIM KONTAKT

TE Part #179463-1
POWER DBL LOCK CAP HSG F/H 2P



Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_928344-2_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_928344-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_928344-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English

Agency Approvals

[VDE Certificate](#)

English