



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**

Element Type: **Thick Film**

Package Size Code: **2512**

Power Rating: **1 W**

Resistance Value: **.62 Ω**

[All Thick Film Resistor: Current Sense \(796\)](#)

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	1 W
Resistance Value	.62 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.6 mm[.024 in]
Product Length	6.35 mm[.25 in]
Product Width	3.1 mm[.122 in]



Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # CAT-C339-R529
Thick Film Resistor: Current Sense

TE Part # 6-1622824-1
RL73N 1J R10 5% 5K RL



Also in the Series | CGS RL73



Surface Mount Resistors(856)

Customers Also Bought




TE Part #1-5177986-1
0.8FH,P06H.5,040,08/Sn,TR,SC




TE Part #2176070-4
3521 13R 1% 2W



TE Part #770904-3
MINI UMNL SOK 22-18 AWG AU




TE Part #282844-2
TERMI-BLOK PCB MOUNT 90 2P.




TE Part #350629-8
.062 COMM P&S PIN PRE TIN/PHBZ



TE Part #1757836-4
AMPLIMITE,R/A RCPT ASY,109,ZN,4



TE Part #1-215297-4
14P HV100 REC CON. TE, 7.0MM



TE Part #1-215309-5
2X15P HV100 REC CON. TE, 8.5MM



TE Part #770894-2
02P SL156 HSG W/THRU BD LATCH



TE Part #1757835-2
AMPLIMITE,PLUG ASY,R/A,109,ZN,2

Documents

Product Drawings

RL73H 3A R62 1% 1K RL

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_9-1622824-3_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1622824-3_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1622824-3_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Standard Tantalum Capacitors - Type TYTS Series - Tyco Electronics Passives](#)

English

[SMD Low Ohmic Current Sense Resistors - Type RL73 Series](#)

English