

RQ73C2B48R7BTD

✓ ACTIVE

Holsworthy | Holsworthy RQ73

TE Internal #: 6-2176388-7

Precision Resistor, Thin Film, 1206, .4 W, 48.7 ohm, .1 %, ±10 ppm/°C, Solder, 2 Termination, Height .55 mm [.022 in], Holsworthy RQ73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor
Element Type: Thin Film
Package Size Code: 1206
Power Rating: .4 W
Resistance Value: 48.7 Ω

Features

Product Type Features

Shelf Life	2 Years
Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	1206

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	.4 W
Resistance Value	48.7 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------



Number of Terminations2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.05 mm[.12 in]
Product Width	1.55 mm[.061 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
ESD HBM Classification	1C
Industry Standard	AEC-Q200 Compliant

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

Passive Component Comment	Shelf Life Based on Date of Manufacture
---------------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2176372-6 RQ 0603 56K2 0.1% 10PPM 5K RL	 TE Part # 2176371-8 RQ 0603 5K49 0.1% 10PPM 5K RL	 TE Part # 3-2176382-0 RQ 0805 267K 0.1% 10PPM 5K RL	 TE Part # 3-2176389-4 RQ 1206 237R 0.1% 10PPM 5K RL
 TE Part # 4-2176391-2 RQ 1206 33K2 0.1% 10PPM 5K RL	 TE Part # 6-2176383-7 RQ 1206 48R7 0.1% 10PPM 1K RL		


Also in the Series | Holsworthy RQ73

Surface Mount Resistors(3078)


Customers Also Bought

 TE Part #5227726-3 ISOLATED BNC SOLDER JACK ASSY	 TE Part #206433-1 CPC RECPT ASSEMBLY SIZE 11-8	 TE Part #205203-8 CRIMP SNAP RCPT ASSY,SIZE 1	 TE Part #5745782-6 15 MSFL RCPT RA 318 (SL,FM)
---	---	--	---





TE Part #205089-1
HD 20 PIN CONTACT



TE Part #205090-1
HD 20 SOCKET CONTACT



TE Part #2-66101-0
III+ SKT,18-16,TIN,SMPACK



TE Part #4-2176388-9
RQ 1206 31R6 0.1% 10PPM 5K RL



TE Part #LM31-00000F-001PG
1PSIG LIQUID LEVEL PRESSURE
TRANSDUCER



TE Part #9-2176527-6
3503G 2B 5K36 1% 5K RL

Documents

Product Drawings

RQ 1206 48R7 0.1% 10PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-2176388-7_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-2176388-7_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-2176388-7_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Thin Film Precision Resistors - AEC-Q200 Compliant - Type RQ73 Series

English