

4DB-R108-02

✓ ACTIVE

Buchanan | Buchanan 4DB Series

TE Internal #: 7-1437667-1

Dual Barrier, Printed Circuit Pin, Wire-to-Board, 2 Position, 8.26 mm
[.325 in] Centerline, 1 Row, Buchanan 4DB Series, Barrier Strips

[View on TE.com >](#)



Connectors > Terminal Blocks & Strips > Barrier Strips



Barrier Strip Style: **Dual Barrier**
Bottom Termination Type: **Printed Circuit Pin**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Centerline (Pitch): **8.26 mm [.325 in]**

Features

Product Type Features

Block Style	Flat Bottom
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Levels	1
Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	150 V, 300 V
-------------------	--------------

Body Features

Primary Product Color	Black
Product Orientation	Right Angle
Barrier Strip Style	Dual Barrier

Contact Features

--	--



PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	10 A, 20 A

Termination Features

Bottom Termination Type	Printed Circuit Pin
-------------------------	---------------------

Mechanical Attachment

Screw Head Type	Wire Clamp Combo Head
Screw Plating Material	Zinc Chromate
Screw Material	Steel
Top Termination Type	Wire Clamp Combo Head
Mounting Options	None
Thread Size	6-32
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Thermoplastic Polyamide
Centerline (Pitch)	8.26 mm [.325 in]

Dimensions

Product Length	18.16 mm [.715 in]
Wire Size	.3 – 3 mm ²

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	104
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 6-1437667-3
4DB-R107-02=4DB ASSEMBLY



TE Part # 7-1437667-9
4DB-R207-02=4DB ASSEMBLY

Also in the Series | Buchanan 4DB Series



Barrier Strips(116)



Customers Also Bought



TE Part #213729-9
CPC RECPT ASSEMBLY SIZE 17-14



TE Part #4-1879021-1
SMW3 4R7 5%



TE Part #5745967-4
25 RCPT SP/FMS STD




TE Part #747299-2
15 RCPT SP/FMS STD



TE Part #3-1825059-0
ADF06STTR04=DIP S,FLUSH,SMT-GW



TE Part #87227-3
06 MODII HDR DRST UNSHRD .100




TE Part #282837-4
TERMI-BLOK PCB MOUNT 4P



TE Part #1-1546462-2
4DB-R108-12=4DB ASSEMBLY



TE Part #2-2176614-2
EP 10W (SS) 7R5 5% BULK BOX



TE Part #361510-3
ATUM-12/4-0-STK

Documents

Product Drawings
4DB-R108-02=4DB ASSEMBLY
English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_7-1437667-1_B1.3d_igs.zip
English
Customer View Model
ENG_CVM_7-1437667-1_B1.3d_stp.zip
English
Customer View Model
ENG_CVM_7-1437667-1_B1.2d_dxf.zip
English
Customer View Model



[ENG_CVM_CVM_7-1437667-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1437667-1_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1437667-1_E.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)

English

[1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE](#)

English