



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0402**

Power Rating: **.0625 W**

Resistance Value: **1.87K Ω**

Features

Product Type Features

Shelf Life	2 Years
Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Power Rating	.0625 W
Resistance Value	1.87K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------



Number of Terminations	2
------------------------	---

Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
ESD HBM Classification	0
Industry Standard	AEC-Q200 Compliant

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

Passive Component Comment	Shelf Life Based on Date of Manufacture
---------------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2176372-6 RQ 0603 56K2 0.1% 10PPM 5K RL	 TE Part # 2176371-8 RQ 0603 5K49 0.1% 10PPM 5K RL	 TE Part # 3-2176382-0 RQ 0805 267K 0.1% 10PPM 5K RL	 TE Part # 3-2176389-4 RQ 1206 237R 0.1% 10PPM 5K RL
 TE Part # 4-2176391-2 RQ 1206 33K2 0.1% 10PPM 5K RL	 TE Part # 6-2176360-2 RQ 0402 1K87 0.1% 10PPM 1K RL		

Also in the Series | Holsworthy RQ73

Surface Mount Resistors(3078)

Customers Also Bought

 TE Part #2-5499206-2 A/L UNIV HDR 14P VERT LG LAT BLUE	 TE Part #4-2176070-3 3521 560R 1% 2W	 TE Part #1-770178-0 06P MINI-UMNL ASSY VO SNNI*	 TE Part #5-104071-4 20 SYSTEM 50 HDR SRST SHRD SN
---	---	--	--



TE Part #2173157-2
MICRO USB, TYPE B, SPLASHPROOF



TE Part #1676165-2
RN 0805 11K 0.1% 10PPM 1KRL



TE Part #5-146252-5
10 MODII HDR DRST B/A .100 LF



TE Part #0460-245-1290
PIN, SOLID, SIZE 12, EXTENDED PCB, SN



TE Part #EEC-325X4B-E016
ENCLOSURE, 3.25 X 4, CLR, NO VENT

Documents

Product Drawings

RQ 0402 1K87 0.1% 10PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-2176363-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-2176363-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-2176363-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Thin Film Precision Resistors - AEC-Q200 Compliant - Type RQ73 Series

English