

## Han-Eco 16B Outd-HBM-with SL



Image is for illustration purposes only. Please refer to product description.

Part number	19 43 216 0340
Specification	Han-Eco 16B Outd-HBM-with SL
HARTING eCatalogue	<a href="https://b2b.harting.com/19432160340">https://b2b.harting.com/19432160340</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® B
Type of hood/housing	Bulkhead mounted housing

### Version

Size	16 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

## Material properties

Material flammability class acc. to UL 94 (locking levers) V-0

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

## Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
Approvals	CE

## Commercial data

Packaging size	1
Net weight	133.4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140179554
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors