





LOC	DIST	REVISIONS					
DF	A5	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED PER ECO-11-000354	12JAN2011	RL	RPW
			B	REV. PER ECO-11-011392	09JUN2011	RJM3	DM



—SILICON SEAL BOOT 4 PLC,
ASSEMBLY SHOWN FOR
REFERENCE, BOOTS ARE
INCLUDED IN KIT.



—CONTACT TYCO ELECTRONICS FOR STANDARD
HARDWARE FOR CONNECTOR ATTACHMENT

- △ CONNECTOR KIT INCLUDES QUADRAx CONTACTS (TYCO ELECTRONICS PART# 1445693-3, QTY 4)
FOR 100Ω CABLE.

2. RECOMMENDED CABLES :
RAYCHEM, CEC-RWC-18687, CEC-RWC-18664
TENSOLITE, NF24Q100, NF26Q100.

- 3 CONNECTOR IS MARKED WITH TYCO ELECTRONICS PART#, LOGO, CAGE CODE & DATE CODE.

4. OPERATING TEMPERATURE RANGE: -65°C TO 125°C (-85°F TO 257°F).


5. SILVER PLATED, STAINLESS STEEL RETENTION CLIPS ARE INSTALLED IN THE CONNECTOR.

- 6 RECESSED CIRCUIT IDENTIFICATION .007±.003 DEEP, CHARACTER
HEIGHT .040±.010.

- 7 CONNECTOR KIT INCLUDES QUADRAx CONTACTS (TYCO ELECTRONICS PART #1445693-5, QTY 4)
FOR 100Ω CABLE.

- △ 8 RECOMMENDED CABLES:
DRAKA, F4704-4
NEXANS, KD24

		2000317-2
		2000317-1
PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06 JUN 2007 CHK D. FABIAN R.P. WALTER APVD B. YOHN		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±.0020 ANGLES ±1°		NAME LOW PROFILE RECTANGULAR QUADRAX 404 ASSY, PLUG, SIZE 3	
MATERIAL		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-2000317	RESTRICTED TO -
				SCALE 2:1	SHEET OF REV B