



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 7 Watt, 200-2M Ohm



Resistor Type: **Power Resistor**
Element Type: **Metal Film**
Power Rating: **5 W**
Resistance Value: **15K Ω**
Resistance Class: **1k Ω – 1M Ω**

[All SMD Power Resistor: 7 Watt, 200-2M Ohm \(316\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Power Rating	5 W
Resistance Value	15K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	6.8 mm[.268 in]
Product Length	13.5 mm[.531 in]



Product Width	7.3 mm[.287 in]
---------------	-----------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Industry Standards

Moisture Sensitivity Level	1
ESD HBM Classification	2
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMF515KJT

Power Resistor, Metal Film, 5 W, 15K ohm, 5 %, ±100 ppm/°C, Solder, 2 Termination, Height 6.8 mm [.268 in], Length 13.5 mm [.531 in], CGS SM





TE Part # CAT-C339-SM1

SMD Power Resistor: 7 Watt, 200-2M Ohm



TE Part # 1879233-9

SMW5 R22 5%

Also in the Series | CGS SM



Battery Holders(1)



Expanded Beam Fiber Optics(9)



LC Connectors(1)



RJ14 Connectors(1)



RJ22 Connectors(1)



RJ25 Connectors(1)



RJ45 Connectors(3)



SC Connectors(2)



Surface Mount Resistors(554)

Customers Also Bought



TE Part #3-640441-4

04P MTA100 CONN ASSY WHT



TE Part #66505-9

SOCKET CONTACT, 20 DF



TE Part #3-1879234-2

SMD Power Resistor: 7 Watt, 200-2M Ohm



TE Part #3-640426-4

04P MTA156 CONN ASSY 18AWG ORA

SMF515KJT

Power Resistor, Metal Film, 5 W, 15K ohm, 5 %, ±100 ppm/°C, Solder, 2 Termination,
Height 6.8 mm [.268 in], Length 13.5 mm [.531 in], CGS SM



TE Part #1-406541-1
[MJ,INV,1X1,6PNL G.,100"ST,SN](#)

TE Part #9-1614882-8
[CPF 0603 20R 0.1% 25PPM 1K RL](#)

TE Part #2337019-1
[UMCC Micro-Coax receptacle, Gen 1](#)

TE Part #4-2176398-7
[3502 1M1 1%](#)

TE Part #4-1618388-6
[LEV200A5NAA=RELAY, SPST-NO](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_3-1879234-6_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1879234-6_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1879234-6_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[SMD Moulded Power Resistor - Type SM Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English