

RP73D1J4K53BTG

✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 8-1879745-9

Precision Resistor, Thin Film, 0603, .1 W, 4.53K ohm, .1 %, ±15 ppm /°C, Solder, 2 Termination, Height .45 mm [.018 in], Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0603

Power Rating: .1 W

Resistance Value: 4.53K Ω

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	75 V
Power Rating	.1 W
Resistance Value	4.53K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]



Usage Conditions

Temperature Coefficient	±15 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Cut Tape Length
------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RP73D1J4K53BTG

Precision Resistor, Thin Film, 0603, .1 W, 4.53K ohm, .1 %, ±15 ppm/°C, Solder, 2 Termination, Height .45 mm [.018 in], Holsworthy RP73



TE Part # 9-1879252-4
RP 2B 10R 0.1% 15PPM CUT LENGTH

TE Part # 5-1879267-0
RP 2B 1M0 0.1% 15PPM 1K RL

TE Part # 2-1879747-4
RP 1J 110K 0.1% 15PPM CUT LENGTH

TE Part # 5-1879743-7
RP 1J 18R2 0.1% 15PPM CUT LENGTH

TE Part # 2-1879279-6
RP 2A 75K 0.1% 15PPM 1K RL

Also in the Series | Holsworthy RP73

Surface Mount Resistors(4556)

Customers Also Bought

TE Part #2-2176055-5
RLP73K 2B R10 1% 1K RL

TE Part #1-794065-0
08P MINI UMNL HDR W/DH SN

TE Part #1969507-2
250 FASTON HSG.,FLAG,REC.,1 POS, NATRUAL

TE Part #2-1879745-1
RP 1J 887R 0.1% 15PPM CUT LENGTH

TE Part #CONMCX001-SMD-T
MCX Jack 50 Ohm PCB Surface Mount

TE Part #CONSMA002-L-G
SMA Jack 50 Ohm PCB Through Hole



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-1879745-9_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-1879745-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-1879745-9_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

RP73-0915

English