





REV.	ECN NO.	DATE	SIGN	DESCRIPTION






With Liquid Glue



Pin Assignments
Front View




Recommended Panel Cut-out



Note:

- * (QC) Important Dimension To Check.
- * Waterproof Rate: IP68
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 5A
- * Flame Class: UL94V-0 (UV Resistance)
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Nut: Nylon+GF, Black
- * Gasket: Silicone, Gray
- * Panel Thickness Max: 4.5mm

UNIT:mm



TOLERANCE
X ±0.25

TITLE
X Lok B-Size
Receptacle M Conn M 4 Pin

SCALE
2:1

SIZE
A4

SHEET
1 OF 1

REV.
A

WC-REV.
A.1

(QC): Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO
BD-04RMMS-QC8001

DWG NO
BD-04RMMS-QC8001

CUSTOMER
ALTW

DRAWN BY
Micky

CHECKED BY
Spring

APPROVED BY
Kevin

DATE
2014-10-20

DATE
2014-10-20

DATE
2014-10-20