

# Han 3M-Hood Top Entry M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 003 1445
Specification	Han 3M-Hood Top Entry M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19370031445">https://b2b.harting.com/19370031445</a>

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han® M
Type of hood/housing	Hood

## Version

Size	3 A
Version	Top entry
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/housings for rough environments
Pack contents	With seal screw

## Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44
	IP65 With seal screw
	IP67 With seal screw

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

## Specifications and approvals

Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	63 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140128385
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors