



Powering Business Worldwide

pe.eaton.com

Eaton Bussmann series time-delay fuse

MDQ-3-1/2

UPC:051712183345

Dimensions:

- **Height:** 1.25 IN
- **Length:** 1.25 IN
- **Width:** .25 IN

Weight:.001 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Electronic- small dimension
- **Application:** Electronic relay and control circuits
- **Amperage Rating:** 3/5A
- **Voltage Rating:** 250 Vac, 32 Vdc (self certified)
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** Axial Leads
- **Response Time:** 60 min maximum at 135%,
120 s maximum at 200%
- **Material:** Glass tube with nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end
- **Number Of Elements:** Dual

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- Not Applicable



