

HPP V4 USB 2.0 A, PFT insert



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	USB
Element	Adapter PCB
Specification	USB 2.0 type A
Adapter for	Jack to pin header

Version

Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

Material properties

California Proposition 65 substances	Naphthalene
--------------------------------------	-------------

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	7 g
Country of origin	Germany
European customs tariff number	85366930
GTIN	5713140061019
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

Mounting instruction

