




Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Hood & Base Locking Device Type: **Locking Clip**

Sealable: **Yes**

Features

Product Type Features

|                                    |              |
|------------------------------------|--------------|
| Hood & Base Connector Product Type | Base Housing |
| Sealable                           | Yes          |

Mechanical Attachment

|                                 |              |
|---------------------------------|--------------|
| Hood & Base Locking Device Type | Locking Clip |
|---------------------------------|--------------|

Housing Features

|                  |                   |
|------------------|-------------------|
| Housing Material | Die Cast Aluminum |
|------------------|-------------------|

Usage Conditions

|                     |     |
|---------------------|-----|
| Corrosion Protected | Yes |
|---------------------|-----|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC  | Compliant |
|                              |           |



|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                          |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JAN 2022 (223)<br>SVHC > Threshold:<br>Pb (.35% in Component)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                                                                                                                                                                                                                                                                                                           |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                                                                                                                                                                                                                                                                                                               |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                          |                                                                                                                                            |                                                                                                                                            |                                                                                                                                            |
|------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # T1320240121-000<br/>H24B-TG-RO-PG21</p> |  <p>TE Part # T1330240129-000<br/>H24B-TSH-RO-PG29</p> |  <p>TE Part # T2040242201-000<br/>HE-024-F</p>        |  <p>TE Part # T1310240121-000<br/>H24B-TS-RO-PG21</p> |
|  <p>TE Part # T1320240125-000<br/>H24B-TG-RO-M25</p>  |  <p>TE Part # T1330240121-000<br/>H24B-TSH-RO-PG21</p> |  <p>TE Part # T1330240132-000<br/>H24B-TSH-RO-M32</p> |  <p>TE Part # T1330240140-000<br/>H24B-TSH-RO-M40</p> |



|                                                                                                                                             |                                                                                                                                                      |                                                                                                                                                       |                                                                                                                                                       |
|---------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <div>TE Part # T1340240125-000<br/>H24B-TGH-RO-M25</div>  |  <div>TE Part # T1340240129-000<br/>H24B-TGH-RO-PG29</div>         |  <div>TE Part # T1340240132-000<br/>H24B-TGH-RO-M32</div>          |  <div>TE Part # T1340240140-000<br/>H24B-TGH-RO-M40</div>          |
|  <div>TE Part # T1320240129-000<br/>H24B-TG-RO-PG29</div> |  <div>TE Part # T1180242540-000<br/>H24B-TGH/TSH-RO-M40/M25</div> |  <div>TE Part # T1180243232-000<br/>H24B-TGH/TSH-RO-M32/M32</div> |  <div>TE Part # T1180244032-000<br/>H24B-TGH/TSH-RO-M32/M40</div> |
|  <div>TE Part # T1310240125-000<br/>H24B-TS-RO-M25</div> |  <div>TE Part # T1320240132-000<br/>H24B-TG-RO-M32</div>         |  <div>TE Part # T1320240225-000<br/>H24B-TG-RO-2M25</div>        |  <div>TE Part # T1330240125-000<br/>H24B-TSH-RO-M25</div>        |

Also in the Series

HDC IP65




Rectangular Connector Hoods & Bases  
(1258)

Customers Also Bought

|                                                                                                                                      |                                                                                                                                       |                                                                                                                                        |                                                                                                                                        |
|--------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
|  <div>TE Part #T1509161000-000<br/>H16A-AGS</div> |  <div>TE Part #T2040102101-000<br/>HE-010-M</div> |  <div>TE Part #T2040062101-000<br/>HE-006-M</div> |  <div>TE Part #T2010162101-000<br/>HA-016-M</div> |
|--------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|





Documents

Product Drawings

H24B-AG-LB

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_T1500243000-000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1500243000-000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1500243000-000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications



Application Specification

English