

## Han 24B Ex-HSE-M25-reel



Image is for illustration purposes only. Please refer to product description.

Part number	19 36 024 1541
Specification	Han 24B Ex-HSE-M25-reel
HARTING eCatalogue	<a href="https://b2b.harting.com/19360241541">https://b2b.harting.com/19360241541</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> Ex
Type of hood/housing	Hood

### Version

Size	24 B
Version	Side entry
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Connectors for explosion hazardous environments
Details	ATTENTION! Only to be used with Han <sup>®</sup> Ex inserts!

### Technical characteristics

Limiting temperature	-20 ... +40 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 With cable gland

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

## Commercial data

Packaging size	1
Net weight	1 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140181885
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors