

Han HVE HOOD SIDE ENTRY



Image is for illustration purposes only. Please refer to product description.

Part number	19 34 010 0521
Specification	Han HVE HOOD SIDE ENTRY
HARTING eCatalogue	https://b2b.harting.com/19340100521

Identification

Category	Hoods/Housings
Series of hoods/housings	Han Hv E [®]
Type of hood/housing	Hood
Type	Low construction

Version

Size	24 B
Version	Side entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Double locking lever
Field of application	Special hoods/housings for Han Hv E [®] screw terminal

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	240 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140128255
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors