



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1377175-0
SMP 0-0926521-1

Customers Also Bought



TE Part #1011-310-0205
CLIP, PA66, BLK, FIR-TREE, ST



TE Part #180916
FF 250 TAB HSG 1P NYLON NAT



TE Part #154719-2
PL 250 REC HSG 1P NYLON RED




TE Part #160860-2
FF 250 REC 0.5-1.0MM2 TPBR



TE Part #1-160759-1
250 PL MKI REC. 20-15AWG PTBR



TE Part #154719-1
250 HSG. PL MKI REC. NAT



TE Part #174045-2
040 MULTILOCK PLUG 12P



TE Part #2112594-1
6POS,NANOMQS,REC HSG,ASSY, SEALED



TE Part #NB08192001
HTAT-8/2-0-STK



TE Part #160914-2
FF 250 REC 4-6MM2 TPBR

Documents

Product Drawings

PL 250 REC HSG 2P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926521-1_L.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_926521-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926521-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English