

86529-000

✓ ACTIVE

TE Internal #: 86529-000

TE Internal Description: FLS503-51 LIQUID LEVEL SENSOR

[View on TE.com >](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

| | | | |
|---|--------------------------------------|-------------------------------------|---|
| | | | |
| TE Part #2-1462037-7 IM06TS=IM RELAY 140mW 12V | TE Part #2-1676913-6 YR1 0.1% 1K0 | TE Part #1623927-8 CFR16 5% 120R | TE Part #3-1625892-7 3W SM M/OX 5% 2K2 |



TE Part #1SNK505910R0000
ES4



TE Part #CB5141-000
HRSR-060FR-10



TE Part #5053052016
RNF-100-3/16-2-STK



TE Part #5728236001
CGPT-R-6.4-0



TE Part #420494-000
RMW-50/16-1200/ADH-0



TE Part #1SNK145011R0000
MC512PA 1->100 Horizontal