



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**
Connector & Housing Type: **Tab Housing**
Number of Positions: **4**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Tab Housing

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Connector & Keying Code	C
Primary Product Color	Natural

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment Type	Polarization
-----------------------	--------------



Mating Retention Type	Locking Lance
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Polyamide
Centerline (Pitch)	5 mm[.196 in]

Dimensions

Product Length	30.5 mm[1.2 in]
----------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	200
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability














Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 9-927742-3 FASTIN FASTON HOUSING 3POS	 TE Part # 9-927742-2 2POS FASTIN FASTON HOUSING	 TE Part # 293009-1 4 POS. FASTIN-FASTON CONN. TAB HOUSING R	 TE Part # 964492-2 2 POS FASTIN/ON HOUSING PANEL MOUNT
 TE Part # 5-964492-5 FASTIN FASTON HOUSING 5POS	 TE Part # 1241857-5 5 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 927742-6 6 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 293011-1 5 POS. FASTIN-FASTON CONN. TAB HOUSING R
 TE Part # 927742-2 2 POS FASTIN/ON HOUSING PANEL MOUNT	 TE Part # 7-927742-6 6 POS. FASTIN-FASTON* TAB HSG RAST5	 TE Part # 1955416-1 3 POS. FASTIN-FASTON CONNECTOR TAB HOUSI	 TE Part # 927742-4 4 POS FASTIN/ON HOUSING PANEL MOUNT
 TE Part # 1241969-8 FASTIN FASTON HOUSING 8P	 TE Part # 293161-1 5 POS. FASTIN-FASTON* TAB HSG, RAST5	 TE Part # 5-927742-3 3P FF FLACHSTGH6,3	 TE Part # 5-927742-6 6 POS FASTIN/ON HOUSING PANEL MOUNT






TE Part # 6-927742-6
6 POS FASTIN/ON HOUSING PANEL MOUNT



TE Part # 9-1241857-5
5POS. FASTIN-FASTON* TAB HSG, RAST5



TE Part # 927742-5
5 POS FASTIN/ON HOUSING PANEL



TE Part # 927742-7
7P FF FLACHSTGH6,3

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)




Connector Contacts(14)



Crimp Terminal Housings(39)




Insertion & Extraction Tools(1)



PCB Headers & Receptacles(417)



Rectangular Connector Housings(1)



Standard Edge Connectors(32)



Standard Rectangular Connectors(63)




Wire-to-Board Connector Assemblies & Housings(202)


Customers Also Bought



TE Part #1744416-2
2 POS EP II HSG, GLOW WIRE




TE Part #794831-1
MINI UMNL SKT SN 22-18 AWG



TE Part #160887-4
FF 110 TAB 0.5-1.0MM2 PTPPB



TE Part #175034-1
PL 187 REC 20-14 AWG 0.30 X 14.0 SS



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-927742-4_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-927742-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-927742-4_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

RAST Connector System Catalog

English

Product Specifications

Product Specification

English

Agency Approvals

VDE Certificate

English

