



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150072-1
OCEAN_2.0_Applicator-E-055F080F-REM

TE Part # 180436-2
110 FASTON,REC.,26-18 AWG,TPBR

TE Part # 2150072-2
OCEAN_2.0_Applicator-E-055F080F-REA

TE Part # 2232974-1
187 FASTON,REC.,24-20 AWG,BR

KIT
TE Part # 7-2150072-7
OCEAN_2.0_SPARE_PART_KIT-055F080F

TE Part # 60674-1
205 FASTON REC 26-22 AWG TPBR

Also in the Series

FASTON 187

Crimp Terminal Housings(41)

Insertion & Extraction Tools(1)

Joints & Splices(1)

PCB Terminals(42)

Quick Disconnects(208)

Splices(1)

Customers Also Bought

TE Part #338095-8
MICRO-MATCH COSI HSG.

TE Part #480115-3
FF 250 REC HSG 2P NYLON BLACK

TE Part #640418-2
BLADE REC 250 18-14AWG TPBR

TE Part #353293-4
MINI CT MT REC ASSY 4P GRAY



TE Part #338096-1
MICRO-MATCH COSICNT



TE Part #5-292228-6
1.5 MINI CT SGL H SMT W/O BOSS



TE Part #292231-3
1.5 MINI CT SGL V SMT W/O BOSS



TE Part #292231-4
1.5 MINI CT SGL V SMT W/O BOSS



TE Part #6-292228-4
1.5 MINI CT SGL H SMT W/O BOSS



TE Part #ES2100401BGM
ES2100401BGM=RELAY

Documents

Product Drawings

187 FASTON REC 24-20 TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_60573-1_AK.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60573-1_AK.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60573-1_AK.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report



English