




Part Number : [395311002](#)
Product Description : 5.08mm Pitch Eurostyle
Vertical PCB Header, 2 Circuits
Series Number : 39531
Status : Active
Product Category : Terminal Blocks and
Barrier Strip



Documents & Resources


Drawings
[Drawing 395311002_sd.pdf](#)

3D Models and Design Files
[3D Model 395311002_stp.zip](#)

Specifications
[Product Specification PS-39500-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39531
Description	5.08mm Pitch Eurostyle Vertical PCB Header, 2 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Family	Terminal Blocks & Barrier Strips
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350543767

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Entry Angle	N/A
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Polyamide

Number of Rows	1
Orientation	Vertical
Panel Mount	No
PC Tail Length	3.30mm
PCB Thickness - Recommended	3.18mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Horizontal Plugs	<u>39530</u>
5.08mm Pitch Eurostyle Vertical Plugs	<u>39533</u>
Mates With	Most 5.08mm Pitch Industry Standard Plugs