

Han PushPull SCRJ WDF coupling



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 242 0333
Specification	Han PushPull SCRJ WDF coupling
HARTING eCatalogue	https://b2b.harting.com/09352420333

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	SCRJ
Element	Panel feed through
Specification	AIDA compliant
Type of contact	SC contact
Features	Intuitive locking mechanism

Version

Shielding	Unshielded
Number of contacts	2
Locking type	PushPull
Pack contents	Without contacts

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14) IEC 61754-24 Mating face
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	17.86 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140054448
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)