







MX PN	TYPE	COLOR
885361100	APC	GREEN
885361101	SINGLE MODE	BLUE
885361102	MULTIMODE	BEIGE



RECOMMENDED MOUNTING CUTOUT
FOR 1.8MM THICK PANEL



ISO VIEW
WITH DUST CAPS

NOTE:

1. ALL MATERIALS SUED IN ADAPTER MEET UL 94 V-0.
2. ALL DMENSIONS ARE FOR REFERENCE ONLY.

ENTER DESCRIPTION EC NO: MF2017-0055 DRWN:SDXIE CHKD: APPR:HXZOU A		2016/08/22 2016/08/24	DESCRIPTION REV	QUALITY SYMBOLS <div>F_A=0</div> <div>F_C=0</div> <div>F_P=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION <div></div>	
						mm	INCH	DRAWN BY SDXIE	DATE 2016/08/22	TITLE SC ONE BODY ADAPTER			
4 PLACES			± ---	± ---	CHECKED BY		DATE						
3 PLACES			± ---	± ---	APPROVED BY HXZOU		DATE 2016/08/24	<div>molex</div>					
2 PLACES			± ---	± ---									
1 PLACE			± 0.15	± ---	MATERIAL NO. SEE TABLE								
0 PLACE			± ---	± ---									
			ANGULAR ±1/2°		DOCUMENT NO.		SD-88536-185		SHEET NO. 1 OF 1				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
					SIZE A 4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							