






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-05-19	Wes	Change Rev.01 To Rev.A




White Printing



Pin Assignments
Front View



Recommended Panel
Cut-Out



- Note:
- * Important Dimension To Check.
 - * Waterproof Rate: IP68(Unmated)
In 1 meters water within 24hours.
 - * Working Voltage Rating: AC 300V
 - * Working Current: 20A
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Liquid Glue: Black
 - * Nut: Nylon+GF, Black
 - * Gasket: Silicone, Gray
 - * Panel Thickness Max: 3.6mm

UNIT:mm		TITLE X-Lok D Size 20A(For Power) Receptacle Rear 3P M Conn F Pin		Amphenol LTW		ITEM NO DC-03RMFS-QC800P	DRAWN BY Wes Fan	DATE 2016-05-19
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 3:2	SIZE A4	SHEET 1 OF 1	DC-03RMFS-QC800P	DWG NO	CHECKED BY Spring Liu	DATE 2016-05-19
REV. A		WC-REV. A.2	QC: Inspection item		ALTW	CUSTOMER	APPROVED BY Kevin Hu	DATE 2016-05-19

安費諾亮泰企業股份有限公司