



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Current Sensing Resistor**

Element Type: **Thick Film**

Package Size Code: **2512**

Power Rating: **2 W**

Resistance Value: **.464 Ω**

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	2 W
Resistance Value	.464 Ω
Resistance Class	Up to 1k Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions





Product Height	.74 mm[.029 in]
Product Length	6.35 mm[.25 in]
Product Width	3.1 mm[.122 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±50 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

RLC73PD3AR464FTDG

Current Sensing Resistor, Thick Film, 2512, 2 W, .464 ohm, 1 %, ±50 ppm/°C, Solder, 2 Termination, Height .74 mm [.029 in], CGS RLC73





TE Part # 8-2176607-9

RLC73PD 3A R464 1% 1K RL

Also in the Series | CGS RLC73



Surface Mount Resistors(2392)

Customers Also Bought



TE Part #4-1879233-1

SMW5 4R7 5%



TE Part #1-1393243-0

RTE24024



TE Part #6-1393238-8

RTD14024



TE Part #1-1879417-1

CPF 0603 470K 0.1% 25PPM 1K RL




TE Part #5-2176339-4

CRGCQ 0603 270K 1%



TE Part #CSJ-SGFB-100-MHF4

SMA to MHF4 100mm 0.81 OD



TE Part #215307-7

2X7P HV100 REC CON. TE, 7.0MM



TE Part #172142-3

EIS LOW PROFILE HSG 3P NATURAL



TE Part #1775838-2

mSATA/mini PCI-E 5.6H Type I G/F



Documents

Product Drawings

RLC73PD 3A R464 1% 2K RL

English

CAD Files

Customer View Model

ENG_CVM_CVM_8-2176605-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-2176605-9_BA.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_8-2176605-9_BA.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic - Current Sense Resistors - Type RLC73 Series

English