




Switches > Push Button Switches



Configuration (Pole-Throw): **Double Pole - Double Throw**

Push Button Switch Product Type: **Anti-Vandal Switch**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Push-On/Push-Off

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC

Body Features

Actuator Force	357 g[12.6 oz]
Case Material	PBT



Product Orientation	Vertical
Actuator Profile	Flush
Bushing Style	Threaded

Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------

Housing Features

Process Sealed	Yes
----------------	-----

Dimensions

	22 in
--	-------

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2213771-1
AV22 SPM 3A NO LED

TE Part # 2213772-5
AV22 SPM 3A MOVE RING LED RED 12V

TE Part # 5-2213772-5
AV22 DPM 3A MOVE RING LED GREEN 24V

TE Part # 1-2213772-3
AV22 SPM 3A MOVE RING LED GREEN 12V

TE Part # 1-2213772-7
AV22 SPM 3A MOVE RING LED BLUE 12V

Also in the Series | Alcoswitch AV22

Push Button Switches(124)

Customers Also Bought

TE Part #1612618-4
SEMI-HARD TRAY DDR2 SODIMM SOCKET 200P 9

TE Part #1734795-1
RJ45,8P8C,SHD,W/O LED,DIP 6u"

TE Part #3-2213767-9
AV19 SPL 3A MOVE RING LED BLUE 24V

TE Part #5-2213772-5
AV22 DPM 3A MOVE RING LED GREEN 24V





TE Part #3-1734795-1
RJ45,8P8C,SHD,W/O LED,DIP, 6u"Au



TE Part #354314-E
DRCBTB 1,27 50 M BTB34 32,2 137 * 094 TR



TE Part #DRC16-70SC
PLG, 70P, BLK, N, C



TE Part #154807-E
SMCB 50 F AB VV 7-13 CL * H007 137 E002



TE Part #214013-E
SRCA 1,27 6 M 1 SMD 137 E1 094 * GURT *

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-2213772-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-2213772-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-2213772-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals

UL Report

English