








8X 0.025
[0.64]
SQUARE

0.18±0.02
[4.5±0.5]

LIQUID
GLUE
SILICONE



CUSTOMER DRAWING

- NOTES:
1. IP67 RATED WHEN PROPERLY ASSEMBLED.
 2. PANEL THICKNESS MAX OF 0.169 [4.30].
 3. ALL PARTS SHIPPED ASSEMBLED.
 4. MATERIALS;
HOUSING AND PANEL NUT - NYLON, BLACK
GASKET- EPDM RUBBER, BLACK
 5. THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
B	28436	11/01/21	PC	TJK
A	28311	08/24/20	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

SolidWorks CAD File (B)

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE		WIDTH		MULT		LBS/M		TEMPER		
FINISH SPEC No.					MATERIAL SPEC No.					
FIRST USED ON				SCALE 2:1		Switchcraft®				
DATE DRAWN 6/23/20		BY FM	CHKD FM 6/23/20		APVD TJK 7/31/20					
NAME RJ45 CAT6 PANEL MOUNT, UNSHIELDED JACK, PC TERMINAL							PART No. ENDP6PC			REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDP6PC](#)