



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (.14% in Component Part)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #6609046-4
Single Phase Filters, Corcom T Series



TE Part #6609037-9
20EP1=F7773 S0



TE Part #85-015G-FC
15 PSIG FLUSH MOUNT PRESSURE
SENSOR



TE Part #5-1419102-4
PCB Power Relay: 30 Amp,
Monostable DC







TE Part #5207952-1
KIT SCREWLOCK FEMALE



TE Part #FX1901-0001-0025-L
FX1901-0001-0025-L



TE Part #2841150-1
QUIK-COMBO connector assembly



TE Part #86-100G-CT
NISO,LP,GAGE,CBL/CONNECT/TUB

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_FX1901-0001-0010-L_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_FX1901-0001-0010-L_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_FX1901-0001-0010-L_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FX19

English