



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **3**
Terminal Orientation: **Straight**
Primary Product Color: **Black**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features



Housing Material	Polyamide
Centerline (Pitch)	8.35 mm[.328 in]

Dimensions

Product Length	27.8 mm[1.09 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 925176-5
FF 312 3P HOUSING REC POLYAMID 6.6 BLACK

TE Part # 281091-2
FF 375 REC 6-10MM2 TPBR

TE Part # 925015-1
FF 110 REC HSG 3P NYLON BLACK

TE Part # 480100-1
FF 312 REC HSG 3P NYLON BLACK

TE Part # 150653-1
FF 312 REC HSG 3P NYLON BLACK

TE Part # 880137-2
3W FASTIN-ON REC. HSG

TE Part # 925306-2
FF 312 REC HSG 3P NYLON CLEAR

Also in the Series | FASTIN-FASTON 375

Crimp Terminal Housings(9)

Insertion & Extraction Tools(1)

Quick Disconnects(19)

Customers Also Bought

TE Part #42663-2
FF 312 REC 16-12AWG TPBR

TE Part #DT04-12PA-P004
REC, 12P, GRY, N, A

TE Part #1394522-1
MIXED SOCKET HOUSING, 42POS. ,

TE Part #2098252-1
PIN, SF, SIZE 16, 14-16 AWG, AU/SN

TE Part #CH04396001
RBK-RTP-125-NR500-2-27MM

TE Part #344073-1
8 WAY TAB HSG.BLACK

TE Part #964455-1
KONTAKTSICHERUNG16P

TE Part #964693-1
KONTAKTSICHERUNG



Documents

Product Drawings

FF 312 REC HSG 3P NYLON BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_925306-3_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_925306-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_925306-3_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English