

CRGP1210F10R

✓ ACTIVE

Neohm | Neohm CRGP

TE Internal #: 2176329-1

General Purpose Resistor, Thick Film, 1210, .75 W, 10 ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .55 mm [.022 in], Neohm CRGP

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**

Element Type: **Thick Film**

Package Size Code: **1210**

Power Rating: **.75 W**

Resistance Value: **10 Ω**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	1210

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	.75 W
Resistance Value	10 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.1 mm[.122 in]



Product Width	2.6 mm[.102 in]
---------------	-----------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGP1210F10R

General Purpose Resistor, Thick Film, 1210, .75 W, 10 ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .55 mm [.022 in], Neohm CRGP



TE Part # 2176326-2
CRGP 0603 12R 1%

TE Part # 5-2176327-4
CRGP 0805 270K 1%

TE Part # 2-2176328-3
CRGP 1206 680R 1%

TE Part # 6-2176330-1
CRGP 2010 1M0 1%

TE Part # 4-2176331-9
CRGP 2512 100K 1%

Also in the Series | Neohm CRGP

Surface Mount Resistors(432)

Customers Also Bought

TE Part #1623783-1
SQM7 10K 5% (METAL FILM)

TE Part #2007198-1
SFP+ 1x1 Cage Assembly, Press-

TE Part #5-1879233-9
SMW5 27R 5%

TE Part #1759547-1
mSATA/mini PCI-E 7H G/F

TE Part #6-104935-3
14 MTE HDR SRRA LTCH.100CL LF

TE Part #2-2176337-9
CRGCQ 0402 2K2 1%

TE Part #2176329-3
CRGP 1210 15R 1%

TE Part #1468976-2
HALL-BRAKE-LIGHT-SWITCH 2, P176

CRGP1210F10R

General Purpose Resistor, Thick Film, 1210, .75 W, 10 ohm, 1 %, ±100 ppm/°C,
Solder, 2 Termination, Height .55 mm [.022 in], Neohm CRGP



Documents

Product Drawings

CRGP 1210 10R 1%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176329-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2176329-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176329-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CRGP Data Sheet

English