



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. CONTACT RESISTANCE: 1 OHM MAX.
 4. RATING: 1A @ 5-24VDC
 5. ELECTRIC LIFE: 50,000,000 CYCLES
 6. OPERATING TEMP.: -20°C to 65°C
 7. ▲ DENOTES CRITICAL PARAMETER.
 8. HARDWARE SUPPLIED: O-RING and HEXNUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID	
B	ECO-101926	UPDATE NOTES	05/19/23	JS	TITLE PZ7M1CRRW300			100120947	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV
					1:1	2/8/2022	MW	T070104	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PZ7M1CRRW300](#)