



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories >

DEUTSCH DRB Mounting Accessories



Automotive Connector Accessory Type: **Mounting Frame**

Primary Product Material: **PA GF**

Primary Product Color: **Black**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All DEUTSCH DRB Mounting Accessories \(6\)](#)

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Frame
-------------------------------------	----------------

Configuration Features

Number of Positions	102, 128
---------------------	----------

Body Features

Primary Product Material	PA GF
Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	Not tested
------------------------	------------

Packaging Features

Packaging Quantity	12
--------------------	----



Packaging Method	Box
Other	
Serviceable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D781-CH8172
DEUTSCH DRB Housings



TE Part # 3320-002-0078
FLANGE CLIP

Also in the Series | DEUTSCH DRB



Automotive Connector Caps & Covers (1)

Automotive Connector Locks & Position Assurance(20)

Automotive Housings(19)

Connector Strain Relief(1)

Insertion & Extraction Tools(1)

Other Automotive Connector Accessories(6)

Customers Also Bought

TE Part #DRB12-128PAE-L018
DEUTSCH DRB Housings

TE Part #WB-51PAL
DEUTSCH DRB Wedgelocks

TE Part #2112166-2
SLIDE, FOR 21POS.

TE Part #K1128729
Battery Disconnecter 35-314-131-S-901

TE Part #DT04-4P-LE11
REC, 4P, BLK, N, CAP, FLANGE

TE Part #1534188-1
21 POS TAB HSG ASSY

TE Part #6-967630-1
FLACHSTE-GEH2,8 21P

Documents

Product Drawings
FLANGE, MOUNT, 102/128P, BLK, STUD, A
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_YDRBM-3A0000000000_A_c-ydrbm-3a0000000000-a.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_YDRBM-3A0000000000_A_c-ydrbm-3a0000000000-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDRBM-3A0000000000_A_c-ydrbm-3a0000000000-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English