

Han 34 HPR - carrier hood 4xM40



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 134 0643
Specification	Han 34 HPR - carrier hood 4xM40
HARTING eCatalogue	https://b2b.harting.com/19401340643

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR EasyCon
Type of hood/housing	Carrier hood
Description of hood/housing	Angled

Version

Size	34 HPR
Cable entry	4x M40
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque (screw locking)	4 Nm
Tightening torque	6 Nm Protection cover 1.5 Nm Inserts
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
-------------------------	---

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	EPDM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Commercial data

Packaging size	1
Net weight	1,391 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140175440
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors