




CGS | CGS 3430

TE Internal #: 7-2176566-9

Power Resistor, Thick Film, 1225, 3 W, 1.6K ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .65 mm [.025 in], Length 3.2 mm [.126 in], CGS 3430

[View on TE.com >](#)

Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**
Element Type: **Thick Film**
Package Size Code: **1225**
Power Rating: **3 W**
Resistance Value: **1.6K Ω**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Film
Package Size Code	1225

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	3 W
Resistance Value	1.6K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2



Dimensions

Product Height	.65 mm[.025 in]
Product Length	3.2 mm[.126 in]
Product Width	6.4 mm[.252 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

3430A3F1K6TDF

Power Resistor, Thick Film, 1225, 3 W, 1.6K ohm, 1 %, ±100 ppm/°C, Solder, 2 Termination, Height .65 mm [.025 in], Length 3.2 mm [.126 in], CGS 3430





TE Part # 7-2176564-9

3430 A3 1% 1K6 100ppm 4k RL

Also in the Series | CGS 3430



Surface Mount Resistors(1168)

Customers Also Bought



TE Part #3-1879074-5

THS15 470R 5%



TE Part #NB16042001

RT-375-3/16-X-STK




TE Part #8149574001

MT3000-1/8-0-SP




TE Part #0333214001

MT3000-1/16-0-SP




TE Part #3-2176566-0

3430 A3 1% 15R 200ppm 1k RL




TE Part #3-2176566-1

3430 A3 1% 16R 200ppm 1k RL




TE Part #3-2176566-7

3430 A3 1% 30R 100ppm 1k RL



TE Part #6-2176566-4

3430 A3 1% 390R 100ppm 1k RL



TE Part #6-2176566-7

3430 A3 1% 510R 100ppm 1k RL



Documents

Product Drawings

3430 A3 1% 1K6 100ppm 1k RL

English

CAD Files

Customer View Model

ENG_CVM_CVM_7-2176566-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-2176566-9_BA.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_7-2176566-9_BA.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet - CGS 3430 Series

English

Automotive Grade Wide Terminal Chip Resistor - Type 3430 Series

English