

Part number	GKTAAT0-H005WN-LS00
Termination	solder
Size	12 [STD 38999]
Locking principle	break , push , screw
Coding	a_key_amc
Cable Diameter	cable amc t h

CODING:A



POSITIONS: 5 positions



PANEL CUT OUT:



DIMENSIONS:



Contact insert description

Number of contacts	5
Contact type	sockets
Contact diameter	16mm
Insulator material	peek
Wire cross section	16-20_awg
Termination	solder

Nominal current single contact	13_a	iec_60512_5_2
Test voltage	18 kv ac	eia 364 20f

Mechanical and environmental data

Degree of protection*	ipsk8_ip6k9k
Operating temperature	65_175_c
Mating cycles	500

1 / 2

Material and surface treatments

Housing	alu_tin_nickel
Contact	cu_alloy_gold

safety_text_2
data_text
ul_text
illustrative_text