

## Han-Yellock 10 hood M20 top entry



Image is for illustration purposes only. Please refer to product description.

Part number	11 20 003 1400
Specification	Han-Yellock 10 hood M20 top entry
HARTING eCatalogue	<a href="https://b2b.harting.com/11200031400">https://b2b.harting.com/11200031400</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Hood

### Version

Locking type	Push button
Size	Han-Yellock® 10
Version	Top entry
Cable entry	1x M20
Field of application	Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)
Material (locking)	Polyamide (PA) Stainless steel



Pushing Performance

## Material properties

Colour (locking)	Melon yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	179.22 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors