



All Single Phase Filters, Corcom FB Series (9)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-M8794
[MRI LED Lighting Filters, Corcom](#)



TE Part # CAT-C8114-F299A
[Single Phase Filters, Corcom FB Series](#)



Also in the Series | Corcom FB

Single Phase Filters(9)

Customers Also Bought

TE Part #2-644486-8
08P MTA100 SHRDED HDR ASSY SN

TE Part #9-1609095-1
5FB3=F8363

TE Part #640311-5
MINI AMP-IN 22-18 AWG POST TIN PLTD

TE Part #8-1393104-1
KRPA-14DG-110=KRPA

TE Part #1624000-3
SC30-10-2525-10 10UH AMMO 1000

TE Part #1969608-5
5P VAL-U-LOK TPA 22-18 AWG

TE Part #36149
PIDG R 22-16 COMM 22-18 MIL 6

TE Part #6609034-9
20VDK1=F7620 S0

TE Part #CSI-RSFB-300-UFFR
RP-SMA to U.FL/MHF1 300mm 1.13 OD

Documents

Product Drawings
3FB3-MS=F8440

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_6-1609128-4_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1609128-4_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1609128-4_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Corcom Combined Selector Charts](#)

English