


线材规格书

STYLE 品名	PVC INSULATED 105°C 300V HOOK UP WIRE	DATE 日期	2011-8-18
SIZE 规格	UL2651 28AWG 7/0.12TS CONDUCTOR	REV 版本	A0
ITEM 类型	YB-XXP-28#-7/0.12TS-1.27		
STANDARD 标准:	UL758 UL1581 C22.2		
APPLI CATION 用途:	INTERNAL WIRING OF APPLIANCES AND ELECTRONIC EQUIPMENT		
CONSTRUCTION 加工:			

CONDUCTOR 导体	SIZE 规格	28 AWG		
	CONSTRUCTION 结构	7/0.12±0.005mmTS		
	MATERIAL 材质	TINNED COPPER CONDUCTOR		
	CONDUCTOR DIAMETER 导体直径	0.34mm		
INSULATION 绝缘	MINIMUM THICKNESS 最小厚度	0.21mm		
	AVERAGE THICKNESS 平均厚度	0.26mm		
	COLOR 颜色	UL2651 棕红橙黄绿蓝紫灰白黑 FLAT CABLE		
JACKET 外被	DIAMETER 外径	0.9±0.1		
	MATERIAL 材质	105°C PVC		
	PITCH 间距	1.27±0.15mm		
	MARKING 印字	无		
ELECTRIC 电气 FUNCTION 功能	RATE VOLTAGE 额定电压	300 V		
	VOLTAGE-WITHSTAND 耐电压	1500 V		
	COND. RESISTANCE 导体电阻	MAX: 239Ω/KM 20°C		
	INSU. RESISTANCE 绝缘电阻	MIN: 10MΩ/KM 20°C		
	TENSILE STRENGTH 抗张强度	老化前	1500PSI	老化后
	ELONGATION 伸长率	老化前	100%	老化后

				1290 PSI (85%)	
				75% (65%)	

FLAT / WIRE CABLE 排线电线:



制作:	王绍富	审核:		核准:	
-----	-----	-----	--	-----	--