





DIMENSIONS mm (inches)



METHOD OF INSERTION
ON THE PCB = FLAT ROCK



PCB LAYOUT



SPECIFICATION 972 or FILF= Nothing in cavities 10 to 17 row a / b / c

LEAD FREE P/N
86093728194755FILF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8609-0000C

rev	ecn no	dr	YY/MM/DD
A	LS08-0148	HLE	2008/04/15
B	LS08-0164	HLE	2008/07/16
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 		mm 		
										TOLERANCES UNLESS OTHERWISE SPECIFIED		
Dr	LE GALLIC	2008/04/15	ANGULAR	LINEAR	0.X		± 0.1	size A3	Scale 1.5			
Eng	LE GALLIC	2008/04/15			0.XX		± 0.1					
Chr	LEGARE	2008/04/15			0.XXX		± 0.1					
Appr	LEGARE	2008/04/15	0.XX' ± 2°					ECN		LS08-0164		
Product family			DIN 8609			Spec ref			-			
			STRAIGHT RECEPTACLE - STYLE C					dwg no		C-8609-1225		Rev.
PRESS FIT												B
catalog no			see table					CUSTOMER		sheet		of