

PORTABLE ANTENNAS SPOTS!



SMA FEMALE STANDARD - FLUSH BASE - T2 (SFJ TYPE)

CODE 22

LARSEN PN	CONNECTOR	FREQUENCY RANGE	ANTENNA TYPE	PERF. RATING	APPROX. LENGTH
SPWB22155	SMA F T2	136-174	Wide Band VHF	*****	9"
SPHL22136	SMA F T2	130-142	Helical - Standard - 1/4 Wave	****	7"
SPHS22136	SMA F T2	132-140	Helical Short - 1/4 Wave	**	3"
SPHL22140	SMA F T2	134-146	Helical - Standard - 1/4 Wave	****	7"
SPHS22140	SMA F T2	136-144	Helical Short - 1/4 Wave	**	3"
SPHL22144	SMA F T2	138-150	Helical - Standard - 1/4 Wave	****	7"
SPHS22144	SMA F T2	140-148	Helical Short - 1/4 Wave	**	3"
SPHL22152	SMA F T2	146-158	Helical - Standard - 1/4 Wave	****	7"
SPHS22152	SMA F T2	148-156	Helical Short - 1/4 Wave	**	3"
SPHL22156	SMA F T2	150-162	Helical - Standard - 1/4 Wave	****	7"
SPHS22156	SMA F T2	152-160	Helical Short - 1/4 Wave	**	3"
SPHL22160	SMA F T2	154-166	Helical - Standard - 1/4 Wave	****	7"
SPHS22160	SMA F T2	156-164	Helical Short - 1/4 Wave	**	3"
SPHL22167	SMA F T2	160-174	Helical - Standard - 1/4 Wave	****	7"
SPHS22167	SMA F T2	162-172	Helical Short - 1/4 Wave	**	3"
SPHL22221	SMA F T2	212-230	Helical - Standard - 1/4 Wave	****	7"
SPHS22221	SMA F T2	214-228	Helical Short - 1/4 Wave	**	3"
SPWB22455	SMA F T2	400-512	Wideband UHF	*****	6"
SPWH22420	SMA F T2	395-445	Whip - Standard - 1/4 Wave	*****	6"
SPHS22420	SMA F T2	403-437	Helical Short - 1/4 Wave	**	2.75"
SPWH22450	SMA F T2	425-475	Whip - Standard - 1/4 Wave	*****	6"
SPHS22450	SMA F T2	432-468	Helical Short - 1/4 Wave	**	2.75"
SPWH22470	SMA F T2	450-490	Whip - Standard - 1/4 Wave	*****	6"
SPHS22470	SMA F T2	452-468	Helical Short - 1/4 Wave	**	2.75"
SPWH22490	SMA F T2	470-512	Whip - Standard - 1/4 Wave	*****	6"
SPHS22490	SMA F T2	475-512	Helical Short - 1/4 Wave	**	2.75"
SPWH22832	SMA F T2	782-882	Whip - Standard - 1/4 Wave	*****	3"
SPEN22832	SMA F T2	792-872	Whip - 1/2 Wave End Fed	****	6.5"
SPHS22832	SMA F T2	800-864	Helical Short - 1/4 Wave	**	2.75"
SPWH22918	SMA F T2	863-973	Whip - Standard - 1/4 Wave	*****	3"
SPEN22918	SMA F T2	873-963	Whip - 1/2 Wave End Fed	****	6.5"
SPHS22918	SMA F T2	872-954	Helical Short - 1/4 Wave	**	2.75"
SPHL22FT	SMA F T2	Field Tunable 136-221	Helical - Standard - 1/4 Wave	****	7"
SPWH22FT	SMA F T2	Field Tunable 400 -512	Whip - Standard - 1/4 Wave	****	7"



SMA FEMALE STANDARD - HALF SKIRT BASE - T3 (SFU TYPE)

CODE 23

LARSEN PN	CONNECTOR	FREQUENCY RANGE	ANTENNA TYPE	PERF. RATING	APPROX. LENGTH
SPWB23155	SMA F T3	136-174	Wide Band VHF	*****	9"
SPHL23136	SMA F T3	130-142	Helical - Standard - 1/4 Wave	****	7"
SPHS23136	SMA F T3	132-140	Helical Short - 1/4 Wave	**	3"
SPHL23140	SMA F T3	134-146	Helical - Standard - 1/4 Wave	****	7"

PORTABLE ANTENNAS SPOTS!

SPHS23140 SMA F T3 136-144 Helical Short - 1/4 Wave ** 3" **SMA FEMALE STANDARD - HALF SKIRT BASE - T3 (SFU TYPE)** **CODE 23**

LARSEN PN	CONNECTOR	FREQUENCY RANGE	ANTENNA TYPE	PERF. RATING	APPROX. LENGTH
SPHL23144	SMA F T3	138-150	Helical - Standard - 1/4 Wave	****	7"
SPHS23144	SMA F T3	140-148	Helical Short - 1/4 Wave	**	3"
SPHL23152	SMA F T3	146-158	Helical - Standard - 1/4 Wave	****	7"
SPHS23152	SMA F T3	148-156	Helical Short - 1/4 Wave	**	3"
SPHL23156	SMA F T3	150-162	Helical - Standard - 1/4 Wave	****	7"
SPHS23156	SMA F T3	152-160	Helical Short - 1/4 Wave	**	3"
SPHL23160	SMA F T3	154-166	Helical - Standard - 1/4 Wave	****	7"
SPHS23160	SMA F T3	156-164	Helical Short - 1/4 Wave	**	3"
SPHL23167	SMA F T3	160-174	Helical - Standard - 1/4 Wave	****	7"
SPHS23167	SMA F T3	162-172	Helical Short - 1/4 Wave	**	3"
SPHL23221	SMA F T3	212-230	Helical - Standard - 1/4 Wave	****	7"
SPHS23221	SMA F T3	214-228	Helical Short - 1/4 Wave	**	3"
SPWB23455	SMA F T3	400-512	Wideband UHF	*****	6"
SPWH23420	SMA F T3	395-445	Whip - Standard - 1/4 Wave	*****	6"
SPHS23420	SMA F T3	403-437	Helical Short - 1/4 Wave	**	2.75"
SPWH23450	SMA F T3	425-475	Whip - Standard - 1/4 Wave	*****	6"
SPHS23450	SMA F T3	432-468	Helical Short - 1/4 Wave	**	2.75"
SPWH23470	SMA F T3	450-490	Whip - Standard - 1/4 Wave	*****	6"
SPHS23470	SMA F T3	452-488	Helical Short - 1/4 Wave	**	2.75"
SPWH23490	SMA F T3	470-512	Whip - Standard - 1/4 Wave	*****	6"
SPHS23490	SMA F T3	475-512	Helical Short - 1/4 Wave	**	2.75"
SPWH23832	SMA F T3	782-882	Whip - Standard - 1/4 Wave	*****	3"
SPEN23832	SMA F T3	792-872	Whip - 1/2 Wave End Fed	****	6.5"
SPHS23832	SMA F T3	800-864	Helical Short - 1/4 Wave	**	2.75"
SPWH23918	SMA F T3	863-973	Whip - Standard - 1/4 Wave	*****	3"
SPEN23918	SMA F T3	873-963	Whip - 1/2 Wave End Fed	****	6.5"
SPHS23918	SMA F T3	872-954	Helical Short - 1/4 Wave	**	2.75"
SPHL23FT	SMA F T3	Field Tunable 136-221	Helical - Standard - 1/4 Wave	****	7"
SPWH23FT	SMA F T3	Field Tunable 400 -512	Whip - Standard - 1/4 Wave	****	7"



SMA MALE FLUSH BASE T2 (SM TYPE) **CODE 24**

LARSEN PN	CONNECTOR	FREQUENCY RANGE	ANTENNA TYPE	PERF. RATING	APPROX. LENGTH
SPWB24155	SMA M T2	136-174	Wide Band VHF	*****	9"
SPHL24136	SMA M T2	130-142	Helical - Standard - 1/4 Wave	****	7"
SPHS24136	SMA M T2	132-140	Helical Short - 1/4 Wave	**	3"
SPHL24140	SMA M T2	134-146	Helical - Standard - 1/4 Wave	****	7"
SPHS24140	SMA M T2	136-144	Helical Short - 1/4 Wave	**	3"
SPHL24144	SMA M T2	138-150	Helical - Standard - 1/4 Wave	****	7"
SPHS24144	SMA M T2	140-148	Helical Short - 1/4 Wave	**	3"
SPHL24152	SMA M T2	146-158	Helical - Standard - 1/4 Wave	****	7"
SPHS24152	SMA M T2	148-156	Helical Short - 1/4 Wave	**	3"
SPHL24156	SMA M T2	150-162	Helical - Standard - 1/4 Wave	****	7"
SPHS24156	SMA M T2	152-160	Helical Short - 1/4 Wave	**	3"
SPHL24160	SMA M T2	154-166	Helical - Standard - 1/4 Wave	****	7"
SPHS24160	SMA M T2	156-164	Helical Short - 1/4 Wave	**	3"
SPHL24167	SMA M T2	160-174	Helical - Standard - 1/4 Wave	****	7"
SPHS24167	SMA M T2	162-172	Helical Short - 1/4 Wave	**	3"
SPHL24221	SMA M T2	212-230	Helical - Standard - 1/4 Wave	****	7"

PORTABLE ANTENNAS SPOTS!

SMA MALE FLUSH BASE T2 (SM TYPE)

CODE 24

LARSEN PN	CONNECTOR	FREQUENCY RANGE	ANTENNA TYPE	PERF. RATING	APPROX. LENGTH
SPHS24221	SMA M T2	214-228	Helical Short - 1/4 Wave	**	3"
SPWB24455	SMA M T2	400-512	Wideband UHF	*****	
SPWH24420	SMA M T2	395-445	Whip - Standard - 1/4 Wave	*****	6"
SPHS24420	SMA M T2	403-437	Helical Short - 1/4 Wave	**	2.75"
SPWH24450	SMA M T2	425-475	Whip - Standard - 1/4 Wave	*****	6"
SPHS24450	SMA M T2	432-468	Helical Short - 1/4 Wave	**	2.75"
SPWH24470	SMA M T2	450-490	Whip - Standard - 1/4 Wave	*****	6"
SPHS24470	SMA M T2	452-488	Helical Short - 1/4 Wave	**	2.75"
SPWH24490	SMA M T2	470-512	Whip - Standard - 1/4 Wave	*****	6"
SPHS24490	SMA M T2	475-512	Helical Short - 1/4 Wave	**	2.75"
SPWH24832	SMA M T2	782-882	Whip - Standard - 1/4 Wave	*****	3"
SPEN24832	SMA M T2	792-872	Whip - 1/2 Wave End Fed	****	6.5"
SPHS24832	SMA M T2	800-864	Helical Short - 1/4 Wave	**	2.75"
SPWH24918	SMA M T2	863-973	Whip - Standard - 1/4 Wave	*****	3"
SPEN24918	SMA M T2	873-963	Whip - 1/2 Wave End Fed	****	6.5"
SPHS24918	SMA M T2	872-954	Helical Short - 1/4 Wave	**	2.75"
SPHL24FT	SMA M T2	Field Tunable 136-221	Helical - Standard - 1/4 Wave	*****	7"
SPWH24FT	SMA M T2	Field Tunable 400 -512	Whip - Standard - 1/4 Wave	****	7"