

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

EVO connector set consisting of: 1407729, 1407730, 1407634, 1407628, 1407670



Your advantages

- Lower costs than metal version
- Labeling option using 9 x 20 mm marking label
- Low weight
- Lower risk of condensation

Commercial data

Item number	1407711
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF63
Product key	BF7AFX
Catalog page	Page 646 (C-2-2019)
GTIN	4046356777766
Weight per piece (including packing)	353 g
Weight per piece (excluding packing)	353 g
Customs tariff number	85366990
Country of origin	CN

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711


<https://www.phoenixcontact.com/us/products/1407711>

Set consists of

HC-B10-I-PT-F - Contact insert

1407729

<https://www.phoenixcontact.com/us/products/1407729>




Contact insert, number of positions: 10+PE, size: B10, number of connections per position: 1, Socket, Push-in connection, 500 V, 16 A, 0.14 mm² ... 2.5 mm², application: Power

HC-B10-I-PT-M - Contact insert

1407730

<https://www.phoenixcontact.com/us/products/1407730>



Contact insert, number of positions: 10+PE, size: B10, number of connections per position: 1, Pin, Push-in connection, 500 V, 16 A, 0.14 mm² ... 2.5 mm², application: Power

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

HC-EVO-B10-BWD-PLRBK - Housing

1407634

<https://www.phoenixcontact.com/us/products/1407634>



HEAVYCON EVO panel mounting base, plastic, B10, with double locking latch, height: 30.5 mm, with flat gasket

HC-EVO-B10-HLFD-PLBK - Housing

1407628

<https://www.phoenixcontact.com/us/products/1407628>



HEAVYCON EVO sleeve housing, plastic, with bayonet flange for EVO screw connection, B10, for double locking latch, height: 60.5 mm, without EVO screw connection

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

HC-B-G-M25-PLRBK - Cable gland

1407670

<https://www.phoenixcontact.com/us/products/1407670>



EVO plastic cable gland with bayonet locking, for housing series B, size M25, cable diameter: 9 mm ... 17 mm

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector
set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Technical data

Product properties

Product type	Connector set
Housing type	Complete housing
Series	HC-B
Type	B10
Number of positions	10
Connection profile	10+PE
Contact numbering	1 - 10
No. of cable outlets	1
Type of the screw connection	1x M25
Protective cover	no
Cable outlet	straight
Pg screw connection	none

Data management status

Article revision	05
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated voltage (III/3)	500 V
Rated surge voltage	6 kV
Rated current	16 A

Connection data

Connection method	Push-in connection
Connection technology	Push-in connection
Conductor cross section	0.14 mm² ... 2.5 mm² (with ferrule)
	0.14 mm² ... 2.5 mm² (with ferrule)
Connection cross section AWG	26 ... 14 (with ferrule)
Tightening torque	0.5 Nm ... 1.7 Nm (Fixing screws for panel mounting base)

Dimensions

[illegible]

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Height	106 mm
Length	93.5 mm
Drill hole distance, horizontal	83 mm
Drill hole distance, vertical	32 mm

Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	65 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material Profile gasket	NBR
Seal material Flat gasket	NBR
Housing material	PA
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Locking latch material	PA

Cable/line

External cable diameter	9 mm ... 17 mm
-------------------------	----------------

Mechanical properties

Mechanical data

Type of the screw connection	1x M25
Locking type	Latch
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 100 °C

Mounting

Thread type	()
Assembly note	Connectors may only be operated when there is no load/the power is switched off. Can be used for solid wires and stranded wires with ferrule.


HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Drawings



Derating diagram


HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Schematic diagram



Pin assignment, connection side, socket


HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Dimensional drawing




Dimensional drawing

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711
<https://www.phoenixcontact.com/us/products/1407711>

Schematic diagram




Pin assignment, connection side, pin

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>



Mounting cutout

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711

<https://www.phoenixcontact.com/us/products/1407711>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407711>

DNV

Approval ID: TAE000037S



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: RU C-DE.BL08.B.00511

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711
<https://www.phoenixcontact.com/us/products/1407711>

Classifications

ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440113

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-EVO-B10PT-BWD-HL-M25-PLRBK - Connector set



1407711
<https://www.phoenixcontact.com/us/products/1407711>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com